



Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Surface mounted box
Range compatibility	Mureva Styl enclosure
Colour tint	Grey (RAL 7016)

Complementary

Device mounting	Surface
Number of gangs	2 gangs horizontal
Cable entry	Easy valve access
Condition of use	Indoor/Outdoor
Material	SEBS PP (polypropylene)
Distance between centers	71 mm
Length	147 mm
Height	54 mm
Width	76 mm
Depth	54 mm

Environment

Quality labels	NF AENOR
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing ≥ 650 °C according to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C