



ENGLISH

Datasheet

RS Pro 12 V, 24 V, 40A Battery Charger

RS Stock No: **851-7496**



Product Details

RS Pro battery charger is a compact automotive charger with pressed steel case. This UK plug type battery charger yields 12 V dc, 24 V dc output voltage at 40 A charge current. It comes with carrying handle that is suitable for regular and low maintenance battery available in 12 V, 6/12 V and 12/24 V versions. This charger has the ability to react to the battery condition and deliver the required charge rate. It is perfect choice for long term care as well as general automotive use.

Features and Benefits

- Trickle and fast charging
- Charging, overload and reverse polarity warning lights
- Ventilation to maintain low working temperature
- Large ammeter display
- Dash mounted fuse for polarity protection
- ASTA/BS approved non-rewirable 3-pin safety plug



ENGLISH

Specifications:

Battery Type Charged	Lead Acid
Number of Charge Stages	2
Plug Type	UK
Charge Current	40 A
Input Current	18 A
Input Voltage	230 V
Output Voltage	12/24 V
Output Voltage @ Charge Current	12 V dc at 40 A, 24 V dc at 40 A