

## 175 1.1/2

### Pipe wrench

Swedish pattern

Code **6437420** ETIM **EC000842**

EAN **4010886643747** UNSPSC **27-11-21-13**

Country of origin **Austria** eCl@ss **21-04-03-01**

Customs tariff number  
**82032000**



### Article description

- Acc. to DIN 5234 Form A
- Particularly solid design for high loads
- Head angled 85 °
- GEDORE special chrome-vanadium steel
- Drop-forged
- Fully tempered, teeth additionally inductively hardened
- Self-gripping by teeth offset against direction of rotation
- Roll nut cannot be lost

### Article information

Contents [Qty of pieces]	<b>1</b>	Standard	<b>DIN 5234 - Form A</b>
Net weight [kg]	<b>1,47 kg</b>	Design non-sparking	<b>No</b>
Total length [mm]	<b>430 mm</b>	Pipe-Ø [mm]	<b>62 mm</b>
Total width [mm]	<b>77 mm</b>	Pipe-Ø [inch]	<b>1 1/2</b>
Total height [mm]	<b>25 mm</b>	Clamping width [mm]	<b>62 mm</b>
Surface	<b>Stove enamelled blue</b>	Hardening process	<b>Induction hardened</b>
Material	<b>Chrome-vanadium steel</b>		