

M18 BHG-502C

M18™ HEAT GUN

- High performance heat coil allows the tool to reach 470 °C
- Reaches operational temperature in six seconds allowing the user to quickly complete his application
- REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- Durable ladder hook for work space management and safety
- Supplied with 2x nozzles: 1x reduction nozzle for heat intensity on a specific area, 1x reflector nozzle to apply heat around an object, such as pipes
- Integrated LED light to illuminate the work area
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Temperature range (°C)	470
Air volume (l/min)	170
Recommended ambient operating temperature (°C)	-18 - +52
Weight with battery pack (EPTA) (kg)	1.4 (M18 B5)
Kit included	2 x M18 B5 Battery packs, M12-18 C Charger, Kitbox
Article Number	4933459772