



See online  
technical sheet

## / MS26 250

1000V Insulated slip-joint adjustable pliers



### / Standards

EN 60900 / IEC 60900 / ISO 5744 / ISO 8976

### / Use

The slimline shape of the head gives it good reach in narrow spaces.

### / Technical specifications

High-performance chromium-vanadium steel : extended lifespan.  
Chrome finish for high anticorrosion protection thanks to a series of 5 baths.  
Inner jaws hardness : 60 HRC for better wear resistance.  
Quick positioning of the required opening.  
Overlapping hinge.

### / Table legend

Overall length tolerance :  $\pm 15$  mm of the nominal value.

## Advantages

- Insulating reinforcements at the ends of arms for protection from impacts.
- Jaws parallel in all opening positions.
- Firm grip on the parts to handle.