

PRODUCT-DETAILS

TC342

2WAY MTG BASE 1.1X1.1IN NAT NYL



General Information

Extended Product Type	TC342
Product ID	7TAG009820R0036
EAN	5414363058465
Catalog Description	2WAY MTG BASE 1.1X1.1IN NAT NYL
Long Description	Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.7mm (0.22 Inches), Two-Component Glue Mounting Method, Bulk Pack

Ordering

EAN	5414363058465
UPC	786210823126

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	14 in 356 mm
Package Level 1 Depth / Length	20 in 508 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	13.3 in 338 mm
Package Level 2 Height	10 in 254 mm

Package Level 2 Depth / Length	21 in 533 mm
--------------------------------	-----------------

Additional Information	
Brand / Label	Ty-Rap
Color	Natural
Effective Date	19680621
Material	Nylon/Polyamide 6.6
Mounting Type	Epoxy Glue (TC2PA)
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Mounting Base
Special Functions	One-piece molding - no lost parts. Consists of one tube each adhesive and activator.

Certificates and Declarations (Document Number)	
Data Sheet, Technical Information	TC342
Instructions and Manuals	TC342
REACH Declaration	9AKK107992A8780
RoHS Information	9AKK107992A8812

Classifications	
ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories	
Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties	

