



Cut



Medium Duty

## Cut-resistant work gloves with an extended knitwrist, deftly blending comfort and dexterity

- **Assured protection:** Developed with INTERCEPT™ Cut Resistance Technology, HyFlex® 11-728 medium-duty safety gloves allow wearers to handle sharper components
- **Elevated comfort:** With a HPPE and Lycra® liner, they deliver superb comfort and flexibility, ensuring sustained worker productivity
- **Strengthened grip:** Designed with PU coating, these industrial gloves boast excellent dexterity and grip in both dry and moderately oily conditions
- **Enhanced features:** Their extended knitwrist afford wearers additional forearm and wrist protection



### Industries

- Automotive
- Construction
- Glass manufacturing
- Machinery and Equipment
- Maintenance
- Metal fabrication
- Aerospace

### Applications

- Assembling metal parts and components
- Assembly of white goods
- Glass repair and replacement
- Press injection molding

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-728

Dexterity with superb cut resistance for optimal productivity

### Key Features

- **INTERCEPT™ Cut Resistance Technology:** Moderate cut protection
- **HPPE and Lycra® liner:** For flexible, dexterous comfort
- **Polyurethane (PU) coating:** Grip in dry or slightly oily environments

### Performance Standards & Regulatory Compliance



### Technologies



### Specifications

| BRAND   STYLE  | DESCRIPTION                                                                                                                                                | Gauge | SIZE               | LENGTH     | COATING COLOR | PACKAGE                      |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|--------------------|------------|---------------|------------------------------|
| HyFlex® 11-728 | <b>Finishing:</b> Palm dipped<br><b>Coating Material:</b> Polyurethane<br><b>Liner Material:</b> Nylon, HPPE, Spandex<br><b>Cuff Style:</b> Long knitwrist | 15    | 6, 7, 8, 9, 10, 11 | 270-320 mm | Grey          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

