

Main

Range of product	Odace
Range	Odace
Product or component type	Central plate
Device presentation	Mechanism with fixing frame
Colour tint	White (RAL 9003)
Quantity per set	Set of 10

Complementary

Product destination	Optical fiber ST connector
Connector type	SC/APC duplex
Device mounting	Flush
Fixing mode	By screws
Material	Thermoplastic ABS-UV stabilised PBT (polybutylene terephthalate) GF30
Surface finish	Glossy
Type of packing	Paint cover
Height	71 mm
Width	71 mm
Depth	27 mm
Net weight	0.02 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...35 °C
Standards	EN 50377-4-1
IP degree of protection	IP20
IK degree of protection	IK04

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes