

MLFB-Ordering data

6SL3202-0AE16-1CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Rated data

Rated current	6.10 A
Power loss	0.090 kW

### Mechanical data

Width	207.0 mm (8.15 in)
Height	175.0 mm (6.89 in)
Depth	72.5 mm (2.85 in)
Degree of protection	IP20 / UL open type
Net weight	3.40 kg (7.50 lb)

### Connections

#### Power connection motor

Version	screw terminals
Conductor cross-section	4.00 mm <sup>2</sup>

#### PE connection

Version	M4 screw studs
---------	----------------