

# Eaton 136283

Catalog Number: 136283

Eaton Moeller® series CSDR Connection cable, 4p, DC current, coupling M12 flat, plug, angled, L=5m

General specifications



Product Name	Catalog Number
Eaton Moeller® series CSDR Accessory	136283
Connection cable	EAN
	4015081330720
Product Length/Depth	Product Height
177.8 mm	25.4 mm
Product Width	Product Weight
152.4 mm	0.27 kg
Certifications	
CE	

## Product specifications

### Type

Connecting cables

### Number Of Poles

Four-pole

### Cable type

Multi-core

Plug, angled, Output side

Coupling, straight, Input side

### Contact surface material

Other

### Rated operational voltage (Ue) - max

0 V

### Product category

Accessories

### Voltage type

DC

### Ambient operating temperature - max

70 °C

### Ambient operating temperature - min

-25 °C

### Continuity resistor

0 mΩ

### Nominal current

0 A

### Cable length

5 m

### Cable sheath material

Other

### Degree of protection

Other

### Color cable sheath

Yellow

### Electrical connection type (box-sided)

M12

### Electrical connection type (field-sided)

M12

## Resources

### Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

### Drawings

[eaton-proximity-switches-csdr-connecting-cable-3d-drawing-002.eps](#)

### Multimedia

[We make what matters](#)

### Wiring diagrams

[eaton-proximity-switches-csdr-connecting-cable-wiring-diagram-003.eps](#)

Contact body material

Other

Permitted temperature of outer cable (assembled) without vibration - max

70 °C

Permitted temperature of outer cable (assembled) without vibration - min

40 °C

Permitted temperature of outer cable (assembling/handling) - max

70 °C

Permitted temperature of outer cable (assembling/handling) - min

40 °C

Plug-in contact type (box-sided)

Male (plug)

Plug-in contact type (field-sided)

Female (bus)

Positioning cable feed (box-sided)

Angled

Positioning cable feed (field-sided)

Straight



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia