

21.5" LED Monitor with BNC Input

Art. no. TVAC10014

Page 1 of 1



- High-contrast 21" LED monitor with bright colour display (16:9 format)
- Full HD resolution: 1.920 x 1.080 pixels
- Connections: 1 x HDMI, 2x BNC input and output for HD-TVI, HD-CVI, AHD and CVBS
- Plug & Play with all conventional analogue technologies
- LED backlighting: Brilliant colour display and high contrast
- Compatible with VESA brackets

Technical Data:

Dimensions	490 x 359 x 147 mm
Connections	1 x HDMI, 2x BNC in/out (TVI, CVI, AHD, CVBS)
Picture format	16:9
Screen diagonal	21,5 "
Width	490 mm
Gross weight	4,1 kg
Display surface	matte
Input	1 x HDMI, 2x BNC (TVI, CVI, AHD, CVBS)
Color levels	16,7 Mio
Housing material	Plastic
Brightness	250 cd/m ²
Height	359 mm
Comb filter	3D

Contrast ratio	1000:1
Length	147 mm
Power consumption	25 W
Max. operating temperature	40 °C
Max. humidity	90 %
Min. operating temperature	0 °C
Monitor type	LED
Net weight	3,7 kg
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V