

Datasheet

6 Piece VDE Screwdriver Set

RS Stock number [623-6463](#)



Material

Chrome molybdenum vanadium steel for Pozidriv
Chrome vanadium steel for Blades
Slotted blades and PP / TPR for handle

Finish

Phosphate black finish screwdriver for blades
Double injection for handle

Hardness

Heat treated to HRV: 52 ~ 56
For slotted screwdriver blades & HRC: 58 ~ 62 for Pozidriv screwdriver blades.

Contents

4 pc-Insulated slotted screwdriver,
Red / black colour double injection
Handle, sizes: 2.5 x 75 mm,
4.0 x 100 mm, 5.5 x 125 mm and
6.5 x 150 mm



ENGLISH

Contents

2 pc-insulated Pozidrive screwdriver,
Red / black colour double injection
Handle, sizes: no.1 x 80 mm,
No.2 x 100 mm. Net weight - 520 g
(Remove the magnet from blade)

Remarks

1. Torque, dimensions and gauge tests meet din-iso- 8764 (din-5262) standard
2. Products are approved by din-en 60900 (Vde 0682) certificate