

RSC51

Service tool trolley with 3 drawers

Main features:

- ABS reinforced worktop, solid and sturdy
- Multipurpose top with anti-fall edges and 8 holes for accommodating screwdrivers
- 3 drawers (588x367 mm) with ball bearing slides, 70 mm high
- Drawer bases protected by foamed rubber mats
- Each drawer can accommodate up to 4 EVA foam or ABS thermoformed trays
- Front centralized safety lock
- Convenient side screwdriver holder included
- Two built-in side spray can holders
- Large lower shelf protected by an anti-oil and anti-petrol rubber mat
- 4 castors, Ø 125 mm: 2 fixed castors and 2 swivel castors (one with brake)

- Static load capacity: 400 kg
- Capacity of each drawer: 15 kg, evenly distributed

 38 kg

Following accessories can be added:

- Wood worktop 2400 RSC24/PL
- Perforated tool panel 2400 RSC24/PF
- PC support 2400 RSC24/SPC
- Folding shelf 2400 RSC24/MP
- Paper roll holder 2400 RSC24/PC-A
- Side tool tray 2400 RSC24AXLP/VL

Completely changed and customizable with accessories!

A must-have for your garage!



	art.		
051000300	RSC51-FO		RAL 2011 - 7016
051000303	RSC51-R		RAL 3000 - 7016
051000307	RSC51-A		RAL 7016

