

## Han 48HPR mounting cover w/o cable entry



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 40 048 9801  |
| Specification      | Han 48HPR mounting cover w/o cable entry                                      |
| HARTING eCatalogue | <a href="https://harting.com/09400489801">https://harting.com/09400489801</a> |

### Identification

|                             |                      |
|-----------------------------|----------------------|
| Category                    | Hoods / Housings     |
| Series of hoods/housings    | Han <sup>®</sup> HPR |
| Type of hood/housing        | Mounting cover       |
| Description of hood/housing | Distance bolt M6     |

### Version

|                      |   |
|----------------------|---|
| Size                 | 48 B  |
| Locking type         | Screw locking                                 |
| Field of application | Hoods/housings for harsh outdoor environments |
| Pack contents        | 4 distance pieces<br>4x M6 screw<br>4 washers |

### Technical characteristics

|  |  |
|--|--|
| Tightening torque (screw locking)      | 4 Nm   |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65<br>IP68<br>IP69 / IPX9K acc. to ISO 20653 |

### Material properties

|                         |   |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast<br>Corrosion resistant |
| Surface (hood/housing)  | Powder-coated                             |



Pushing Performance  
Since 1945

## Material properties

|                                      |                       |
|--------------------------------------|-----------------------|
| Colour (hood/housing)                | RAL 9005 (jet black)  |
| Material (seal)                      | NBR                   |
| Material (locking)                   | Stainless steel       |
| RoHS                                 | compliant             |
| ELV status                           | compliant             |
| China RoHS                           | e                     |
| REACH Annex XVII substances          | Not contained         |
| REACH ANNEX XIV substances           | Not contained         |
| REACH SVHC substances                | Not contained         |
| California Proposition 65 substances | Yes                   |
| California Proposition 65 substances | Nickel<br>Naphthalene |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1                                      |
| Net weight                     | 621 g                                  |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140058378                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |