



Side panel D: 400 mm 1 set = 2 units

Model	
product brand name	SIVACON S4
product designation	side panel
design of the surface	powdered
design of the product EMC version	No
Protection class	
protection class IP	IP55
Appearance	
RAL color number	RAL 7035
color	light grey
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	2 000 mm
width	9 mm
depth	400 mm
net weight	20.5 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



EG-Konf.



VDE



[Confirmation](#)

other	Environment	
Miscellaneous	Environmental Con- firmations	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2520-4BA02>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2520-4BA02>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2520-4BA02

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/4/2025 

