

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010057](#)  
**Status:** **Active**  
**Overview:**  
**Description:** GWconnect Turned Crimp Contact for 10A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 1.00mm<sup>2</sup> (18 AWG), 100 per Bag

**Agency Certification**

CSA	256883
UL	E249674

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Contact Type	Turned Crimp
Overview	hdc_heavy_duty_connectors
Product Category	Contacts
Product Name	GWconnect
UPC	887191867557

**Physical**

Gender	Male
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	0.700/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size AWG	18
Wire Size mm <sup>2</sup>	1.00

**Electrical**

Current - Maximum per Contact	10.0A
-------------------------------	-------

**Material Info**

Engineering Number	7100.4214.0
--------------------	-------------

**Reference - Drawing Numbers**

Sales Drawing	936010051-000
---------------	---------------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400719\_00\_000.pdf

**Search Parts in this Series**

[93601](#) Series

**Mates With**

[93601](#) Female Turned Crimp Contact

**Use With**

S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts