



ENGLISH

United Kingdom 2-Pin Plug-in Power Supply 5vdc 15watt



The RS Pro Range of Class II 15 watt AC/DC United Kingdom plug-in power supplies provide 15 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Features:

- United Kingdom Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved





ENGLISH

Specification	
RS Stock Number	1753307
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	No Damage
Output Voltage Rating	+5V
Output Current Range	3A
Output Min Current	0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Right Angle
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 2%
Ripple & Noise	300mVp-p
Efficiency	80% Min
Over Voltage Protection	25VDC Maximum
Over Load Protection	2.5A max with auto-recovery function
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet T-LICENSE(BS EN60950-1)
EMI Standard	Meet CE(EN55022)
MTBF	50K Hours
Size mm max.	70 (L) 50 (W) * 77 (H) mm
Weight	139g
Regulator Type	Switched Mode Power Supply