

Features

- Medium Duty
- Stainless Steel
- Industrial castor
- Fixed
- Fixing Plate
- Polyamide 6
- Corrosion Resistant
- Impact Resistant
- Shock Absorbing

RS PRO Castor Wheels

RS Stock No.: 0730078



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Polyamide 6 wheel. Hub on plain bore. In pressed stainless steel AISI 304. Assembled with self-locking nut.

General Specifications

Rotation	Fixed
Weight Class	Medium Duty
Load Capacity (Kg)	300
Load Capacity / 4pcs (Kg)	1200
Tyre Material	Polyamide 6
Hub Material	Polyamide 6
Bracket Material	Pressed Stainless Steel
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Industrial castor

Operation Environment Specifications

Operating Temperature (Celsius)	-25° to 85°
--	-------------

						
200x50	140x110	105x80	11x16	235	300	380

Mechanical Specifications

Mounting Type	Single Bolt
Wheel Diameter (mm)	200
Wheel / Tread Width (mm)	50
Overall Height (mm)	235
Number of Fixing Holes	4
Fixing Hole Size (mm)	11x16
Hub Bearing Type	Plain Bore
Thread Size (M)	
Stem Height (mm)	
Stem Diameter (mm)	
Hardness of Wheel (Shore A)	
Levelling Extent (mm)	
Offset (mm)	
Castor Weight (Kg)	2.090

Fixing Centres Specifications

Fixing Centres (mm)	105x80
Fixing Centres Length (mm)	105
Fixing Centres Width (mm)	80

Fixing Plate Specifications

Fixing Plate Dimensions (mm)	140x110
Fixing Plate Length (mm)	140
Fixing Plate Width (mm)	110