



Hand protection

DUOCOLOR VE330

WORK WITH OCCASIONAL CHEMICAL RESISTANCE

Chemical glove, ideal for handling chemicals and micro-organisms



Specific benefits



Durability

· High-quality coating extends the life of the glove and provides excellent protection for the hand



Performance

· Lightweight for optimal dexterity

Applications

- Agriculture
- Finishing works / Craftsmanship
- Manufacturing/Transformation
- Accommodation & Food services
- Maintenance
- Chemical industry

Certifications and norms



EN 388
1 0 1 0 X



EN ISO 374-1
TYPE A
AKLMNPT



EN ISO 374-5



Protects against risks



Biological



Chemical



Particules



Hand protection

DUOCOLOR VE330

WORK WITH OCCASIONAL CHEMICAL RESISTANCE

Chemical glove, ideal for handling chemicals and micro-organisms

Standards - Details



EN388:2016+A1:2018

1 [0-4] ABRASION RESISTANCE
0 [0-5] CUT RESISTANCE
1 [0-4] TEAR RESISTANCE
0 [0-4] PIERCE RESISTANCE
X [A-F] CUT RESISTANCE ISO 13997



EN 374

A : MÉTHANOL
K
L
M
N
P
T

Technical details

Glove kind	Tight glove
Glove family	Tight glove unsupported flocked
Tight glove kind	Unsupported
Inner finition	Flocked
Coating material and finition	Latex double layer
Coating level	Fully coated
Number of layer	Double Layer
Thickness (mm)	0,60
Arm level protection	Forearm cuff (< 400mm)
Color	Blue-Yellow
Size	6, 7, 8, 9, 10
Type of packaging	in individual bags



Safety gloves

DUOCOLOR VE330

WORK WITH OCCASIONAL CHEMICAL RESISTANCE

Chemical glove, ideal for handling chemicals and micro-organisms

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VE330BJ06	Blue-Yellow	6/7	DUOCOLOR VE330	3295249009533	13295249009530	144	12	10.9 kg	46.0 cm	29.0 cm	35.0 cm
VE330BJ07	Blue-Yellow	7/8	DUOCOLOR VE330	3295249009540	13295249009547	144	12	14.0 kg	46.0 cm	29.0 cm	35.0 cm
VE330BJ08	Blue-Yellow	8/9	DUOCOLOR VE330	3295249009557	13295249009554	144	12	12.5 kg	46.0 cm	29.0 cm	35.0 cm
VE330BJ09	Blue-Yellow	9/10	DUOCOLOR VE330	3295249009564	13295249009561	144	12	13.7 kg	46.0 cm	29.0 cm	35.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height