



Fuse-link, low voltage, 4 A, AC 415 V, 80 kA, BS88, 13 x 29 mm, gL/gG, BS



Powering Business Worldwide™

Part no. STREET LIGHTING FUSE >4A 415V
Catalog No. SMD4

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	4
Rated voltage			AC 415 V
Construction size			BS88
Size			13 x 29 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			street lighting cut-outs
Standard/Approval			BS
Shape			cylindrical
Standards/Regulations			BS88-1

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	4
Rated voltage		V	415
Voltage type			AC
Rated switching capacity		kA	10
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No