

Datasheet

RS Pro Straight 50 Ω Cable Mount BNC Connector Plug, Clamp, Solder Termination RG213 Silver

RS Stock No: **546-4358**



Product Details

RS Pro cable mount BNC connector plug has silver plated body, silver plated centre contact and is suitable for RG213 cables. This 50 Ω straight BNC connector plug comes with bayonet coupling and a cable clamp, solder termination. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Silver plated body
- Silver plated centre contact
- Clamp, solder termination

**Specifications:**

Body Orientation	Straight
Body Plating	Silver
Cable Type	RG213
Contact Material	Copper
Contact Plating	Silver
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Clamp, Solder
Operating Temperature Range	-65 to +165°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)