

Eaton 163837

Catalog Number: 163837

Eaton Distribution parts. Fuse switch disconnecter, 3p, NH00, AC23, 00CE

General specifications



Product Name	Catalog Number
Eaton Distribution parts	163837
EAN	Product Length/Depth
4015081603671	590 mm
Product Height	Product Width
49.5 mm	280 mm
Product Weight	Compliances
4.705 kg	RoHS conform

Product specifications

Features

Motor drive optional

Fitted with:

Error protection

Connectors

Rated operational power at AC-23A, 400 V, 50 Hz

0 kW

Rated permanent current (Iu)

160 A

Rated uninterrupted current (Iu)

160 A

Conditioned rated short-circuit current Iq

100 kA

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0 kW

Rated short-time withstand current (Icw)

0 kA

Electrical connection type of main circuit

Screw connection

Actuator position

Front side

Actuator type

Long turning handle

Suitable for

Busbar mounting

Front mounting

Rated conditional short-circuit current (Iq)

100 kA

Suitable for fuses

NH00

Cable entry type

Side

Degree of protection (front side)

IP40

Resources

Declarations of conformity

[03_pift0_110717.pdf](#)

[DA-DC-03_PIFT0](#)

Installation instructions

[IL1470403ZU](#)

Power rating at AC-23, 400 V

0 kW

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia