



## DCG412M2

### 18V XR Li-Ion Grinder

#### Selling Proposition

- Steel cut spiral bevel gears provide highest level of durability and low vibration, increasing user productivity
- Low profile jam pot gear case improves gear durability and ergonomics
- Intelligent trigger & lock-off switch for enhanced work safety & control
- Keyless guard for enhanced application versatility
- Two position side handle offers greater comfort and control
- Quick change wheel release allows quick and easy wheel removal

#### Standard Equipment

- 2 position side handle
- Keyless protective guard
- Blade Wrench
- Multi-voltage charger
- 2 x 4.0Ah XR Li-Ion battery packs with state of charge indicator

#### Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	18 V
Battery Capacity	4.0 Ah
Max. Disc Diameter	125 mm
Power Output	405 Watt
No Load Speed	7000 rpm
Spindle Thread	M14
Weight	2.9 kg