



DCH213L2-XE

18 Volt Lithium Ion Heavy Duty 3 Mode Dedicated Cordless Hammer

Selling Proposition

- Ideal for drilling anchors and fixing holes into concrete, brick and masonry from 4mm to 20mm
- Rotation stop mode for light chiselling in plaster, tiles and render
- Impact stop mode for rotary drilling only in wood, ceramic, steel
- Best in class vibration, 6.9m/s² reduces user fatigue and maximises operating periods
- Bright white LED with delay feature improves visibility and provides flashlight functionality
- Electronic motor brake for additional control

Standard Equipment

- 2 x batteries
- XR multi-voltage charger
- multi-position side handle
- heavy duty carrying case

Warranty Specifications

- 3 Year Limited Warranty (Terms and Conditions Apply)
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Voltage	18 V
Battery Capacity	3.0 Ah
Power Output	300 Watts
No Load Speed	0-1100 rpm
Impact energy (EPTA 05/2009)	2.0 J
Blows per Minute	0-4200 bpm
Tool Holder	SDS-Plus
Max Drill Capacity (Wood/Metal/Concrete)	26 mm/ 13 mm/ 20 mm
Weight	3.0 kg
Length	303 mm
Hand/Arm Vibration	6.9 m/s ²
Uncertainty K1	1.5 m/s ²