



JetNet 3806G

Industrial 4 FE + 2 GbE Unmanaged PoE Switch (Booster)

4 10/100 TX plus two 10/100/1000TX uplink ports
 IP Surveillance with 4 IEEE802.3af PSE
 12/24V Power Input 48V PoE Output
 2 Gigabit Ports for Video Server/IPC connection
 Port Link-Fault Alarm DO
 -25~60°C operating temperature

Facts

General description

| | |
|-------------------|----------------|
| Part number | F00N3806000000 |
| Life cycle status | Mature |
| Warranty | Up to 5 years |

Interface

| | |
|---------------------|----------------------------------|
| Total ports number | 6 |
| 10/100TX ports | 4 |
| 10/100/1000TX ports | 2 |
| DI/DO (dry relay) | 1 relay DO with 1A/24VDC ability |
| DC power input | 1 x DC 12-24V |
| PoE ports | 4 |
| Power feeding mode | 4578 (B) |
| PoE mode | IEEE 802.3af |
| System PoE budget | 60W@24V 60°C |

Features

| | |
|-------------|-----------|
| Switch type | Unmanaged |
|-------------|-----------|

SW/Protocol

| | |
|------------------------|------------|
| Traffic priority (QoS) | Yes |
| Event alarm | Port Alarm |

Mechanical

| | |
|-------------------------|------------------|
| Housing/protection (IP) | IP30 Aluminum |
| Dimension (HxWxD mm) | 149 x 66 x 131.2 |
| Mounting | DIN Rail |
| Operating temperature | -25~60°C |

Certification

| | |
|---------------------|-------------------|
| Regulatory/approval | CE/FCC/UL 62368-1 |
| RoHS | Yes |

People & Technology. Connected.

We are a people company. Our experienced, skilled and passionate people empower you to meet your challenges through best-in-class, user-friendly solutions. We are a technology company. We help you optimize processes through our software, hardware and services, and through our support. Connecting people and technologies gives you the means to accomplish your goals and ambitions, and gain a competitive edge in today's digitalized world.

Visiting address HQ: Stora Varvsgatan 13a

SE - 211 75 Malmö, SWEDEN

[+46 40 35 86 00 \(tel:+46 40 35 86 00\)](tel:+4640358600)

[info@beijerelectronics.com \(mailto:info@beijerelectronics.com\)](mailto:info@beijerelectronics.com)