

## DATA SHEET

## **I4TCOUPL6AIP68**

IP68 CAT6A RJ45 FEMALE-FEMALE FIELD COUPLER

# **BENEFITS**

- IP68 protection level suitable to harsh environments : dustproof & waterproof
- ZAMAC shielding 360°
- 1/4 turn waterproof lock
- Toolless assembly









### **DESCRIPTION / APPLICATIONS -**

- CAT6A RJ45 female/female straight junction coupler for Industrial Ethernet RJ45 CAT6A network
- Field mounting
- IP68 protection rating
- Suitable to harsh environments (industrial, outdoor, ...)
- Ea class link performance
- Zamac shielding to avoid electromagnetic interference

#### NORMS -

- Ethernet base T up to 10Gbits/s
- ISDN

- IEEE 802.3af/at/bt (PoE / PoE+/4pPoE)
- UL 1863

### **ENVIRONMENTAL PROPERTIES** -

#### **OPERATING TEMPERATURE:**

-25°C to +50°C

#### **CONFORM TO:**

RoHS and REACH







# DATA SHEET

### **ELECTRICAL PROPERTIES -**

**CURRENT:** 

1.5A

**CONTACT RESISTANCE:** 

 $20m\Omega$ 

**ISOLATION RESISTANCE:** 

500ΜΩ

**DIELECTRIC WITHSTAND VOLTAGE:** 

1000Vac - 60Hz

#### MECHANICAL / TECHNICAL PROPERTIES -

**COATING:** 

Plastic ring : PA 66 Connector : Zn+Ni alloy

SHIELDING: Zamac

**INSERTION CYCLE:** 750 cycles

**CONTACT:** Bronze, platine Ni+Au 1.2µm

**INSERTION FORCE: 30N** 

### PERFORMANCES -

#### **SYSTEM**

TIA 568-C.2 CAT6A

ISO 11801 Ed3 Class Ea


EN 50173-1

#### APPLICATION

IEEE 802.3af/at/bt (PoE / PoE+/4pPoE)


### DRAWINGS -

















# DATA SHEET

## **ORDER INFORMATION -**

P/N	DESCRIPTION	PACKAGING
I4TCOUPL6AIP68	IP68 Cat6A RJ45 female-female field coupler	Unit

### ASSOCIATED PRODUCTS -



**I4PLUGIP68** IP68 RJ45 CAT6A plug



**I4PLST6AIP68**IP68 RJ45 CAT6A field plug