

RS Stock No:9172343, 9172353, 9172356, 9172460, 9172472, 9172485

## **RS Pro Polyurethane Airline with 3/8" BSPT Couplings**



Designed to overcome the limitations of traditional nylon preformed coil, Polyurethane Compact Coils offer excellent resistance to abrasion, oils and kinking, as well as improved flexibility.

- Preformed with press in swivel couplings complete with springs.
- Excellent resistance to abrasion.
- Very good kink resistant characteristics.
- Complies with current F&DA regulations.
- Useful for confined areas limited by space / bend radius.
- Service Temperature -20°C to + 65°C.
- Maximum working pressure: 10 bar.
- 6m Working length
- 12mm OD
- 30.5 turns
- 500 / 1000mm tail lengths
- 76mm Coil diameter
- Press in 3/8" BSPT press in swivel couplings complete with springs.
- Blue
- Industrial applications using air tools, instrumentation, robotics.