




---

 PRODUCT-DETAILS

# SPLB25/M25/B

## STR SWL NPB FITTING M25 25MM-MET




---

**General Information**

Extended Product Type	SPLB25/M25/B
Product ID	7TCA296100R0159
EAN	5020963007507
Catalog Description	STR SWL NPB FITTING M25 25MM-MET
Long Description	3/4 Inch Nickel Plated Brass Straight Fitting with Swivel External Thread, IP68 Rating, Metric Thread Size M25

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963007507
UPC	786210245454

---

## Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	3/4 Inch

---

## Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963007507
Package Level 1 Height	11.81 in 300 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

---

## Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---

## External Classifications and Standards

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

