

TURCK AS-interface® Physical Media Connectivity

AS-interface®, eurofast® Flat Cable Adapter

- Allows the Mixing of Standard AS-I Flat Cable with *eurofast* Round Cable in Same System
- May be Needed when Going from a Dry to a Wet Environment or an Area Where Better Sealing and Rugged Connectors are Required

Housing Style	Part Number	Specs	Pinout
	ASI-PM-1 BW1239	TPU (Polyurethane) 250 V, 4 A -40° to +75°C	Female
	ASI-PM 41		

	Type	Approvals	Data Pair		Outer Jacket Material Color Nominal O.D.	Bulk Cable Part Number / Weight/300 M
			AWG Color Code	DCR (/1000 feet) Insulation		
	250 105°C 300 Volts		2/16 AWG BU/BN	6.5 Ohms TPE-S	TPE Yellow Flat	RB21603-*M 40 lbs.
	251 105°C 300 Volts		2/16 AWG BU/BN	6.5 Ohms TPE-S	TPE Black Flat	RB21605-*M 40 lbs.
	253 75°C 300 Volts	NEC ITC PLTC CEC [CMG]	2/18 AWG BU/BN	6.5 Ohms PVC	PVC Light Grey Flat	RB50782-*M 42 lbs.
	253G 75°C 300 Volts	NEC PLTC CEC AWM I/II A/B FT4	2/16 AWG BU/BN	4.1 Ohms PVC	TPE Grey Flat	RB51240-*M 42 lbs.
	253BK 75°C 300 Volts	NEC PLTC CEC AWM I/II A/B FT4	2/16 AWG BU/BN	4.1 Ohms PVC	TPE Black Flat	RB51241-*M 42 lbs.
	253Y 75°C 300 Volts	NEC PLTC CEC AWM I/II A/B FT4	2/16 AWG BU/BN	4.1 Ohms PVC	TPE Yellow Flat	RB51242-*M 42 lbs.

* Indicates length in meters.

Standard cable lengths are 1, 2, 4, 5, 6, 8, 10, 15, and in +5 meter increments from there. Consult factory for other lengths.