

# ACS480-04-04A1-4



ACS480-04-04A1-4 Pcont.max:1,5kW, lcont.max:3,8A

## General Information

Global Commercial Alias	ACS480-04-04A1-4
Product ID	3AXD50000047767
ABB Type Designation	ACS480-04-04A1-4
EAN	6438177458951
Catalog Description	ACS480-04-04A1-4 Pcont.max:1,5kW, lcont.max:3,8A

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177458951
Invoice Description	ACS480-04-04A1-4 Pcont.max:1,5kW, lcont.max:3,8A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	FIPSEEXPU US Drive Services SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

## Dimensions

Product Net Height	223 mm
Product Net Weight	1.77 kg
Product Net Width	73 mm

## Additional Information

Product Main Type	ACS480-04-04A1-4
Product Name	Frequency Converter

## Categories

---

Drives → Low voltage AC drives → General purpose drives

Water Utility Solutions → Desalination Plant → Electrical → Drive systems → Drives → Low voltage AC drives → General purpose drives

