

BQ-CC65E ERP

eneloop pro Charger with USB Output



Key Specifications

Parameter	Value
Part Number	BQ-CC65E ERP
Charging bays	1–4 x AA / AAA NiMH (independent channel control)
Input	AC 100–240 V, 50/60 Hz (EU plug variant)
Compatible chemistry	NiMH (eneloop / eneloop pro)
Display	LCD status display
Controls	Refresh, Display, USB Out buttons
USB output	Yes — can charge USB devices from inserted batteries
Charge time (approx.)	≈2 h (quick charge mode)
Safety features	Auto-stop on full charge; rejects non-rechargeable cells
Batteries included	No
Plug region	EU (ERP variant)