

Motorcbl. Q8/0 M 4G2.5+2x2x0.75 EMC 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 201 0291 00
Specification	Motorcbl. Q8/0 M 4G2.5+2x2x0.75 EMC 1.5m
HARTING eCatalogue	https://harting.com/6188201029100

Identification

Element	Motor cable
Specification	Pre-assembled on one side With brake with termic device
Connector 1	Han-Compact® Hood Han® Q 4/2 Male
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Core structure	4x 2.5 mm ² + 2x (2x 0.75 mm ²)
PE contact	Yes
Field of application	for motor connection

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	685 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140274341
eCl@ss	27060490 Ready-made low-voltage line (unspecified)
ETIM	EC002587
UNSPSC 24.0	26121629