

# Carbide drill bits - CIF

Product	Carbide drill bits
	Packaging - box of 10 pcs (more economic), Ø - 0,4 mm : DU64.10
	Packaging - box of 10 pcs (more economic), Ø - 0,5 mm : DU65.10
	Packaging - box of 10 pcs (more economic), Ø - 0,6 mm : DU66.10
	Packaging - box of 10 pcs (more economic), Ø - 0.7 mm : DU67.10
	Packaging - box of 10 pcs (more economic), Ø - 0,8 mm : DU68.10
	Packaging - box of 10 pcs (more economic), Ø - 0,9 mm : DU69.10
	Packaging - box of 10 pcs (more economic), Ø - 1,0 mm : DU70.10
	Packaging - box of 10 pcs (more economic), Ø - 1,1 mm : DU71.10
	Packaging - box of 10 pcs (more economic), Ø - 1,2 mm : DU72.10
	Packaging - box of 10 pcs (more economic), Ø - 1,3 mm : DU73.10
	Packaging - box of 10 pcs (more economic), Ø - 1,4 mm : DU74.10
	Packaging - box of 10 pcs (more economic), Ø - 1,5 mm : DU75.10
	Packaging - box of 10 pcs (more economic), Ø - 1,6 mm : DU76.10
	Packaging - box of 10 pcs (more economic), Ø - 2,0 mm : DU80.10
	Packaging - box of 10 pcs (more economic), Ø - 2,5 mm : DU85.10
	Packaging - box of 10 pcs (more economic), Ø - 3,0 mm : DU90.10
	Packaging - box of 10 pcs (more economic), Ø - 0.3 mm : DU63.10
	Description - Jeu 24 forets Ø 0.8 à 3.2 mm, pas 0.1 mm : DU92
	Description - Jeu 38 forets Ø 0.6 - 0.7 - 0.8 - 1.0 - 1.2 - 3.17 mm : U800020
	Packaging - box of 10 pcs (more economic), Ø - 2,1 mm : DU81.10
	Description - Ring for drill bit or milling bit - distance to cut to be confirmed when ordering, 1 pce : U600002

**Product Image**



---

**Summary**

Monopiece. Reinforced shank Ø3,17Packaged by 10 pieces (more economical)  
• In stock from 0,4 mm to 3,00 mm • Minimum drilling speed 20 000 rpm • Smallest is the diameter, higher will be the speed • Descent speed from 1,6 to 4 m/min • Option: drill bits with ring upon request

---