




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1437667-0
4DB-P208-02=4DB ASSEMBLY



TE Part # 1546927-6
6P .325 TRI-BARRIER W/COVER



TE Part # 5-1437667-9
4DB-P207-06=4DB ASSEMBLY

Customers Also Bought




TE Part #1-2176070-5
3521 39R 1% 2W




TE Part #1622826-2
CRG0402 5% 100K



TE Part #7-1676970-1
RN 0603 402R 0.1% 10PPM 1K RL



TE Part #1-776163-1
35POS,PIN DIA 1.3,HDR ASSY,90DEG, COD 1



TE Part #2108838-1
Chip ant., SMD, BT/Wi-Fi 2.4GHz



TE Part #1625854-3
0603 PROBE PAD



TE Part #3-6318490-6
.5FHR04H,220,S,GIG,08/Sn,HT,NSYes



TE Part #5227161-6
RTANG JK W/MTG PINS, BNC PCB



TE Part #825440-3
MOD 2 PINHDR 2X03P.



TE Part #796681-2
TERMI-BLOK PCB MOUNT 2P.

Documents

Product Drawings

06P .325" HIGH-RISE DUAL BARRI

English

CAD Files

Customer View Model

ENG_CVM_CVM_1546734-6_B1.3d_stp.zip

English

Customer View Model



[ENG_CVM_CVM_1546734-6_B1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1546734-6_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1546734-6_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1546734-6_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1546734-6_B.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE](#)

English

Agency Approvals

[Agency Approval Document](#)

English