

Actuator

45-
2729.1010.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2729.1010.000>

Your product:



45-2729.1010.000

Actuator

FRONT

Front dimension: Ø 29 mm

Front form: Round

Front bezel colour: Black

Front bezel material: Plastic

MOUNTING

Design: Raised

Mounting cut-out: Ø 22.3 mm

Mounting type: Panel mounting

OPERATING-/INDICATION PART

Lens colour: Black

Lens material: Plastic

Lens illumination: Non illuminated

Lens shape: Raised

Lens optics: opaque

Lever colour: Black

Lever material: plastic

Lever shape: round

MECHANICAL CHARACTERISTIC

Switching action: Maintained

Release type:	Twist to unlock
Mechanical lifetime:	300 000 cycles of operation
Operating frequency:	Max. 600/h
Weight:	0.018 kg


AMBIENT CONDITION

IP front protection:	IP66, IP67, IP69K
Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 80 °C
Shock resistance:	According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance:	According to IEC 60068-2-6: 20 ... 500 Hz: 5 g
Climate resistance:	During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6


CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, Raised, Non illuminated, Black, Plastic, opaque, non illuminative, Black, round, Round, Black, Plastic, Maintained, IP66, IP67, IP69K, Twist to unlock
Dimension:	Ø 29 mm
Housing material:	Plastic
Product attributes:	Twist to release, can be latched after pressing by rotating to the right
Wiring diagrams:	

Mounting cut-outs:



Dimension drawings:

