

Eaton 12FDLNJ25

Catalog Number: 12FDLNJ25

Eaton Bussmann series medium voltage DIN fuse, 25 A, AC 12 kV, 2", 51 x 292 mm, fullrange, DIN

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	12FDLNJ25
	EAN 5027590432290
Product Length/Depth	Product Height
360 mm	51 mm
Product Width	Product Weight
51 mm	1598 g
Compliances	Certifications
DIN 43625 VDE 0670-4	IEC60282-1

Product specifications

Type

Fuse

Application

transformer protection
indoor use

Amperage Rating

25 A

Fuse indicator

Non Indicating

Breaking capacity

50 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Full-range

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

No

Class

Class full-range

Fuse diameter

51 mm

Resources

Technical data sheets

[720106 24kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

Interrupt rating

50 kAIC

Construction size

51 x 292 mm

Voltage rating

12 kV



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia