







FBF6 6 ltr AFFF Foam
FBF9 9 ltr AFFF Foam

Fire Rating 13A / 144B
Fire Rating 21A / 183B



-  BSI accredited to BS EN3 & Kitemarked
-  Manufacturer's 5 year warranty
-  Stored pressure - Easy low cost maintenance
-  Safe if used on electrical equipment
-  Suitable for A & B class fires
-  Controlled discharge
-  Supplied with wall-mounting bracket

Refilling/Serviceing: Should be carried out annually to BS 5306 Part 3, 2003. After complete or partial use the extinguisher should be refilled to BS 6643 Part 1, 1985. Both refilling and servicing to be carried out by a competent person. Spares available on request.

Model	FBF6	FBF9
Capacity	6 ltr	9 ltr
Total Weight	10.3 kg	14.5 kg
Total Height	540 mm	610 mm
Total Width (excluding hose)	230 mm	230 mm
Working Temp.	+5 ^o to +60 ^o C	+5 ^o to +60 ^o C
Discharge Time	40 secs	50 secs
Discharge Range	5-6 m	5-6 m
Operating Pressure	12 bar @ 20 ^o C	12 bar @ 20 ^o C
Minimum Burst Pressure	55 bar	55 bar
Packing Specification		
Qty Per Carton	1	1
Carton Dimensions	56x17x18cm	62x20x20cm
Carton Volume	0.017m ³	0.025m ³
Carton Weight	10.7 kg	15 kg
Qty Carton per Pallet	50	40
Pallet Dimensions	120x100x88cm	120x100x100cm
Pallet Volume	1.05m ³	1.2m ³
Pallet Gross Weight	565 kg	630 kg