



Thermal transfer printer

TT431, Small to medium volume printing

The TT431 thermal transfer printer is perfect for printing on HellermannTyton materials such as self-adhesive labels, shrinkable tubing and identification tags. Thanks to its low weight and compact construction, the TT431 integrates seamlessly into any workstation. It is easy to use due to its intuitive touch display and clear status messages which can be shown in multiple languages. The optional cutter and perforator make this printer ideal for a wide range of applications. 300 dpi resolution ensures that barcodes, warning symbols, logos and text are as sharp as they can be.

Features and benefits

- Medium volume single sided printing
- Print on HellermannTyton cable markers and labels
- Uses standard ribbons
- Barcodes: standard and 2D
- Print speed up to 125 mm/s (30mm/s recommended for Ladder Style products and tubing)
- Adjustable label sensor
- Multiple language selection
- Windows drivers: 32/64 bit for Windows XP, Windows Vista, Windows 7, 8, 10



TT431 thermal transfer printer.

Print Method	Thermal transfer
Print Head Type	300 dpi, flat type
Print Speed	up to 125 mm/s
Max. Print Width	106 mm
Label Height Max (metric)	1,000 mm
Interfaces	USB 2.0, Ethernet 10/100 Base T
Supported Barcodes, Printer	Standard and 2D
Printer Memory	64 MB RAM
Dimensions W x H x D	253 mm x 189 mm x 322 mm
Weight	4 kg



One Step to the Web!



TYPE	Article-No.
TT431	556-00400

Subject to technical changes.

TYPE	Description
S431 Cutter	Cutter for TT431
P431 Perforator	Perforator for TT431
TT External Reel Holder	External Reel Holder
TT431 300dpi Printhead	Printhead for TT431
TT431 Print Roller	Print Roller for TT431

Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.