



Sample photo

Order symbol: ALN 081806
Product nbr: 7811170
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016089
EI. number:
 Finland: 3420046
 Electric No. 8212045664
 Denmark:
 Electric No. Sweden: 2536315

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	177	81	57	ARM 0818	DIN-15 Mounting rail
inch:	7.0	3.2	2.2	EKV 12	DIN-35 Mounting rail
Materials:				MR 75003	Selftapping taptite screw M3
Material:	Aluminium			MRS 28540	Wall fastening lug (2 pcs)
Base colour:	RAL 7001			Rating:	
Cover screws material:	Stainless steel			Ingress Protection (EN 60529): IP66/IP67/IP68	
Cover colour:	RAL 7001			Impact Resistance (EN 62262): IK08	
Gasket material:	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-50 ... 140 °C			SGS Fimko	
Temperature °C (continuous):	-50 ... 80 °C				
Temperature °F (short term):	-60 ... 285 °F				
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:					
AM 0818	Mounting plate				

