

218.6337

PLUG
63A 3P+N+E 6h 346-415V 60Hz 50Hz
Mantle terminals



* Product image may be indicative



EN IEC 60309-1 (2022)
EN IEC 60309-2 (2022)
Low voltage direct. 2014/35/EU

GENERAL CHARACTERISTICS

Commercial Series	OPTIMA Series
Synthetical description	PLUG
Description	
The OPTIMA Series plug, designed for high-performance electrical applications, operates at a rated voltage of 346-415V and a rated current of 63A. It features a 3P+N+E configuration with a 6h hour position, compatible with both 50Hz and 60Hz frequencies. the plug offers superior protection with an ip66/ip67/ip69 rating, ensuring resilience against dust and water ingress. Equipped with mantle terminals, it facilitates secure and efficient connections. Available in a straight outlet type, this plug incorporates the EASY-PLUG feature for enhanced usability. A black version is also available by appending “.K” to the catalogue number, catering to diverse industrial requirements.	
Mounting version	PORTABLE

TECHNICAL CHARACTERISTICS

Rated current	63A
Poles	3P+N+E
Hour position	6h
Rated voltage	346-415V
Working frequency	60Hz
	50Hz
Terminals	Mantle terminals

PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
Colour	RED
Material	THERMOPLASTIC
Protection degree	Watertight
Protection degree IP	IP66/IP67/IP69
Protection degree IK	IK08
Types of available outlets	STRAIGHT
Contact material	CuZn (brass)
Surface treatment contacts	Nickel-plated
Cable entry	CABLE GLAND

DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]

OPTIONS & VARIOUS NOTES

Notes	EASY-PLUG
Catalogue notes	Version also available in black; just add “.K” at the end of the catalogue number.