1265 - 1275 : Adjustable Manual Threader



Description

Forged, heat-treated steel, reversible without removal, for right and left-hand threads. Two removable tubular steel handles, can be screwed end to end.

Adjustable rear guides for centring the threader on the pipe.

Opening lever disengages the dies from the pipe when threading completed for trimming metal shavings and removing the threader from the pipe.

References

Sku	Description	Ø ext. tube "	Pipe O.D. mm	Dies	kg
126500	Single ratchet 1" to 3"	1.1/2 - 2, 2.1/2 - 3	40/49 - 50/60, 66/76 - 80/90	Right BSPT	19,100
126520	Single ratchet 1" to 3"	1 - 1.1/4, 1.1/2 - 2, 2.1/2 - 3	26/34 - 33/42, 40/49 - 50/60, 66/76 - 80/90	Right BSPT	20,000
127500	Single ratchet 2.1/2" to 4"	2.1/2 - 3, 3.1/2 - 4	66/76 - 80/90, 90/102 - 102/114	Right BSPT	25,200
126599	Single ratchet housing only	1 - 3	-	-	18,600
127599	Single ratchet housing only	2.1/2 - 4	-	-	23,150

