

Features

- IP65
- Indoor-Outdoor
- Sealable
- 35mm DIN Rail
- Screw Plugs

RS PRO Consumer Units

RS Stock No.: 0818847



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Surface-mounted consumer units, 12 modules, 215x310x110 mm, IP65. This product stands out for its superior quality and optimized design, always ensuring exceptional performance. Compatible with the addition of earth and neutral terminals, includes sealing plugs

General Specifications

Model Number	0818847
Housing Material	ABS
Door Material	PC
Colour	Grey
Transparent Door	Yes

Mechanical Specifications

Height (mm)	215
Length (mm)	310
Width (mm)	110
Dimension (mm)	215x235x110
Weight (kg)	1,005

Electrical Specifications

Electrical Insulation	Class II
Rated current (kA)	10
Dielectric strength (k0818849)	3,75

Protection Category

IP Rating	IP65
IK Rating	IK08

Approvals

Declarations	Declaration of Conformity
Standards Met	IEC/EN 62208:2024, IEC 61349-1:2021, IEC 61439-3:2012

Similar Products

Stock No.	Brand	Product Name	Door Type	No. of Modules	No. of DIN rails
0818844	RS PRO	Surface distribution enclosure	Transparent door	4 modules	1 DIN rail
0818846	RS PRO	Surface distribution enclosure	Transparent door	8 modules	1 DIN rail
0818848	RS PRO	Surface distribution enclosure	Transparent door	26 modules	2 DIN rail
0818849	RS PRO	Surface distribution enclosure	Transparent door	42 modules	3 DIN rail

Stock No.	Brand	Description
0818850	RS PRO	Blank cover plate for 4.5 modules in white-
0818852	RS PRO	Metal lock for IP65 distribution cabinets
0818853	RS PRO	Accessory for wall mounting IP65 distribution cabinets
0818854	RS PRO	Internal plugs to ensure watertightness in IP65 distribution cabinets
0818841	RS PRO	Neutral and ground terminal strip 2x16 mm ² + 4x10 mm ²
0818842	RS PRO	Neutral and ground terminal strip 2x16 mm ² + 12x10 mm ²
0818843	RS PRO	Neutral and ground strip support + 1 RG-12 strip (2x16 mm ² + 12x10 mm ²)

