

ROLINE USB4 Gen3x2 Cable, PD (Power Delivery) 20V5A, with Emark, C-C, M/M, black, 15 cm

Product No.	11.02.9078
Manufacturer	ROLINE
Manufacturer No.	11.02.9078
EAN (single piece)	7630049628595



ROLINE USB4 flat silicone cable with data transfer rates of up to 40 Gbit/s and support of PD (Power Delivery) at up to 20V5A. The silicone-sheathed flat cable not only looks great, but also allows extremely flexible use thanks to its small bending radius.

- USB4 cable in high quality
- With USB type C connectors on both sides
- Suitable for data transfer rates of up to 40 Gbit/s
- USB power supply with up to 20V5A
- Rugged aluminum plugs and a flexible, flat silicone cable for optimal durability
- Supports video transfer
- Colour: black

ROLINE USB4 cable - USB C connector on both sides - Charging and data cable for Smartphones, Tablets, MacBooks or Ultrabooks/Notebooks

The major benefits of the USB4 includes faster transfer speeds (up to 40 Gbit/s), a better management of video bandwidth (using a process called "protocol tunneling" that sends DisplayPort, PCIe and USB packets at the same time while allocating bandwidth accordingly) and optional compatibility with Thunderbolt 3 products.

Technical specifications	
Manufacturer	ROLINE

Product group	Cable
Product type	USB4 Cable
Colour	black
Length	15 cm
Transfer quality	USB4 Gen3x2 40 Gbit/s
Connection ports	USB Type C (USB-C) Male / USB Type C (USB-C) Male
Side 1 Connector Type	USB Type C (USB-C)
Side 1 Connector Gender	Male
Side 2 Connector Type	USB Type C (USB-C)
Side 2 Connector Gender	Male
Colour (Cable)	black
Ribbon cable	yes
Maximum data transfer rate	40 Gbit/s
Area of application	External
Supported charging technology	USB-PD - USB Power Delivery
Power (max.)	100 W
Hand locking screws	no
Depth	150 mm
Weight	11 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	10 mm
Depth of packaging (single piece)	140 mm
Package weight (single piece)	0.017 kg