

tesa® 4329 PV1

Finely creped paper mask tape

The product is thin and flexible and, therefore, suitable for all general masking applications, as well as oven drying applications up to a temperature of 70 °C.

Main Application

- Masking
- Lacquering work
- Good flexibility for curves
- Can be used on painted metal, rubber, glass and chrome parts

Technical Data

▪ Backing material	slightly-creped paper	▪ Elongation at break	10 %
▪ Total thickness	125 µm	▪ Tensile strength	33 N/cm
▪ Type of adhesive	natural rubber	▪ Temperature resistance	70 °C
▪ Adhesion to steel	2.8 N/cm		

Properties

▪ Hand tearability	●●●●	▪ Sharp colour edge	●●●
▪ Easy to remove	yes	▪ Conformability	●●●
▪ Paint anchorage	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=04329>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All technical information and data above mentioned are provided to the best of our knowledge on the basis of our practical experience. They shall be considered as average values and are not appropriate for a specification. Therefore tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. The user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.