

FEATURES

- Grey spade connector
- Wire size range of 1.5 mm² to 2.5 mm², 16 AWG to 14 AWG
- Tab size of 0.8 mm x 6.35 mm
- Length of 13.6 mm
- Unshrouded
- Crimp termination method
- Uninsulated
- Tin-plated brass contacts

RS PRO Grey Uninsulated Spade Connector, 6.35 x 0.8mm Tab Size, 1.5mm² to 2.5mm²

RS Stock No.: 488-1336



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Spade Connectors



Product Description

Use this spade connector to join single wires to relays or components, or in any situation where you need to make fast, reliable connections. This spade connector is made to fit 6.35 mm receptacles and its design allows terminals to be connected and disconnected while the bolt is still partially screwed in.

General Specifications

Insulation	Uninsulated
Orientation	Straight
Shrouded/Unshrouded	Unshrouded
Termination Method	Crimp
Connector Type	Tab
Contact Plating	Tin
Contact Material	Brass
Colour	Grey
Applications	Used in domestic appliances, like dishwashers and washing machines

Mechanical Specifications

Minimum Wire Size	1.5mm²
Maximum Wire Size	2.5mm²
Tab Size	6.35 x 0.8mm
Minimum Wire Size (AWG)	16AWG
Maximum Wire Size (AWG)	14AWG
Tab Thickness	0.8mm
Tab Width	6.35mm
Overall Length	13.6mm



Approvals

Compliance/Certifications

EN61340

