# Box type plug-in units



### **PCB** holder

for box type plug-in units

For fastening PCBs in box type plug-in units.

Polycarbonate, base material to UL 94-V0

Supply includes:

Assembly parts.

Packs of	Model No. RP
2	3606.321

### Detailed drawings:

Available on the Internet.



## Ripac box type plug-in units, type I

### Technical specifications:

- Installation depth: 160 and 220 mm
- Height: 3 U to IEC 60 297-3
- Rear panel to accommodate individual connectors

### Material:

- Front panel: 2.5 mm aluminium
- Rear panel: 2 mm aluminium, natural anodised
- Side panel sections: Extruded aluminium
- Handle: Aluminium
- PCB holder: Plastic

#### Surface finish:

Front panel, side panel sections, handle: Natural anodised



### Accessories:


- Covers, see page 246.
- Guide rails, see page 235.

#### Detailed drawings:

Available on the Internet.

HP	Model No. RP	
ПР	3 U	3 U
Board depth 160 mm		
6	3653.000	-
8	-	3653.010
10	-	3653.020
12	-	3653.030
14		3653.040
21	-	3653.050
28	-	3653.060
Board depth 220 mm		
10	-	3653.200
12	-	3653.210
14	-	3653.220
21	-	3653.230
28	-	3653.240
Supply includes		
Front panel	1	1
Handle	1	1
Side panels	1	2
Cover including rear panel	1	12
Rear panel	-	1
PCB holder	2	2
Assembly parts (set)	1	1





#### Covers

for box type plug-in units, type I

### With vent holes

For slide-in fastening.

#### Material:

1.0 mm aluminium, unplated

#### With vent slots

For screw fastening.

### Suitable for the installation of guide rails.

#### Material:

1.2 mm sheet steel

### Surface finish:

Spray-finished

#### Colour:

**RAL 9006** 

	Packs	Model No. RP	
Unit width of		with vent slots1)	with vent holes
Board dep	th 160 n	nm	
8 HP	1	-	3687.585
10 HP	1	3687.556	3685.683
12 HP	1	3687.557	3685.684
14 HP	1	3687.558	3685.685
21 HP	1	3687.559	3685.686
28 HP	1	3687.560	3685.687
Board dep	th 220 n	nm	
10 HP	1	-	3685.695
12 HP	1	-	3685.696
14 HP	1	3687.565	3685.697
21 HP	1	3687.566	3685.698
28 HP	1	3687.567	3685.699

1) Guide rails for box type plug-in units from 12 HP: For PCB depth 160 mm, packs of 10, Model No. RP 3606.140 For PCB depth 220 mm, packs of 10, Model No. RP 3606.200



## Also required:

Assembly screws, Packs of 100, Model No. RP 3685.289, see page 250.