

233.50.063 25 bar G1/4B center back mount

Bourdon Tube Pressure Gauges, Stainless Steel

Item number:	9452028	
Quantity:	1 pcs.	
Order code:	233.50-C-BG425Z-GB-BZEZCZZ-ZZZZZZZ IZZZZZZ121ZZ LABEL-PG1DE-ZZZZZ	313D4AZIYG0 ZZZ-
Overview:	233.50.063 25 bar G1/4B center back mount Measuring System 316 SS Ingress protection: IP 65 class 1.6 Window: polycarbonate Case filling fluid: glycerine Permissible ambient temperature: -20 ... +60 °C Permissible medium temperature: + 100 °C Pressure Gauge Standard: International (standard Europe) stop-pin at zero *WIKA* with Serial number Label: WIKA standard without / with Tag-number	
Details:	Bourdon Tube Pressure Gauges, Stainless Steel Series Model: 233.50 Specifications according to data sheet: PM 02.02 Measuring system: stainless steel Case filling: with Nominal size: 063 mm Scale range: 0...25 bar Process connection: G 1/4 B Connector location: center back mount Window: polycarbonate Pointer: standard pointer Accuracy class: class 1.6 Overpressure safe: standard Case material: Stainless steel 1.4301 Case surface: bare Material pressure element: Measuring System 316 SS Case filling fluid: glycerine Ingress protection: IP 65 Permissible medium temperature: + 100 °C Permissible ambient temperature: -20 ... +60 °C Movement: stainless steel Packaging: single packing Pressure Gauge Standard: International (standard Europe)	

Date: 23/01/2024



Manufacturer logo: *WIKA*
with Serial number
stop pin on dial: at zero