

PREVOST FILTRATION - SINGLE UNITS

Manually operated pressure relief valve



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Max. operating pressure (bar)	Net weight (Kg)
ATU V100	G1/8	1500.00	12.00	0,319
ATU V101	G1/4	3000.00	12.00	0,319
ATU V102	G3/8	6400.00	12.00	0,766
ATU V103	G1/2	9000.00	12.00	0,776

