




Part Number : [5041950570](#)
Series Number : 504195
Status : Active - Proprietary
Product Category : PCB Headers and Receptacles



Drawings

[5041950570_sd.pdf](#)

Specifications

[AS-504193-001-001.pdf](#)


[AS-504193-002-001.pdf](#)

[SPK-504195-001-001.pdf](#)

[PS-504193-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active - Proprietary
Category	PCB Headers and Receptacles
Series	504195
Description	Micro-Lock 1.25mm Pitch Single-Row Right-Angle Header, Beige, 5 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Micro-Lock
UPC	887191210728

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Beige
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Nickel
Net Weight	184.514/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.20mm, 1.60mm
PC Tail Length	3.00mm
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-25° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Single-Row Crimp Housings	<u>504193</u>