



TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



BENCHTOP VARIABLE TRANSFORMER
MODEL: CMSE5
INPUT: 230-240V
OUTPUT: 0-112% OF INPUT
RATING: 5A MAXIMUM
FUSE: 5A
INPUT LEAD: 2m 15A 3-CORE CABLE WITH
 BS1363 13A UK DOMESTIC PLUG
SOCKET: SAFEBLOCK
 NEUTRAL-EARTH-LIVE



REV

4	
3	
2	
1	

CARROLL & MEYNELL
 TRANSFORMERS LIMITED
 TEL: 01642 617406 FAX: 01642 614178
 enquiries@carroll-meynell.com

TITLE
**BENCHTOP VARIAC
 CMSE5**
 ALL DIMENSIONS IN mm

DRAWN GB	PROJECTION 	DATE 15/02/08	SCALE NTS
DRAW No 5089		REV 0	PAGE 1/1